

TECHSPEC® 510nm CWL, 25mm Dia, 20nm Bandwidth, OD 6 Fluorescence Filter



Stock #87-748 3-4 DAYS

[Additional Bandwidths](#)

⊖ 1 ⊕ **€313,00**

ADD TO CART

Qty 1-5

€313,00

Qty 6+

€258,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Angle of Incidence (°):
0 ±5

Bandwidth (nm):
20.00

OD 6 Blocking Wavelength Range (nm):
300 - 490 & 531 - 800

Optical Density OD (Average):
≥6.0

Clear Aperture CA (mm):
21.21

Center Wavelength CWL (nm):
510.00

Full Width-Half Max FWHM (nm):
25.00

Substrate:
[Fused Silica](#) (Coming 7980)

Minimum Transmission (%):
93

Coating:
Hard Coated

Surface Quality:
60-40

Thickness Tolerance (mm):
±0.1

Transmission (%):
93.00

Type:
Bandpass Filter

Blocking Wavelength Range (nm):
250 - 1100

Construction:
Mounted in Black Anodized Ring

Transmitted Wavefront, RMS:
λ/4 (prior to coating)

Compatible Fluorophore:
Cy2 Emission / Cy3 Excitation

Environmental Durability:
Humidity per ML-STD-810H, Section 507.6
Temperature per ML-STD-810H, Section 501.7 and 502.7

Physical Durability:
Adhesion per ML-PRF-13830B, Section C.4.5.12
Moderate abrasion per ML-PRF-13830B, Section C.4.5.11
Cleaning per ML-C-48497A Section 4.5.4.2

Mount Thickness (mm):
3.5 ±0.1

Substrate Thickness (mm):
2.00 ±0.25

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Compliant](#)