

532nm, 11mm Dia., 5x5 Spot Matrix, Diffractive Beamsplitter



HOLO/OR Diffractive Beamsplitters

Stock **#14-686** 3-4 DAYS

- 1 + **€1.605,00**

ADD TO CART

Qty 1+
€1.605,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
9.2

Coating:
Laser V-Coat (532nm)

Design Wavelength DWL (nm):
532

Diameter (mm):
11.00 +0.05/-0.15

Substrate:

Fused Silica (Coming 7980)	
Thickness (mm):	3.00 ±0.1
Input Beam Mode:	SMor MM
Minimum Beam Diameter (mm):	0.18
Overall Efficiency (%):	74
Full Angle (°) :	2.0 x2.0
Output Number of Spots:	5 x5
Separation Angle (°):	0.50 x0.50
Uniformity (%):	<8
Zero Order, Relative to the Average (%):	0-100
Damage Threshold, Reference: ☐ See Link for More Details	

Regulatory Compliance

RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 233:	Compliant