

TECHSPEC®

5mm Dia. x 15mm FL, NIR II, Inked, Double-Convex Lens



Stock **#67-598-INK** 3-5 DAYS
[Other Coating Options](#)

-

1

+

€59,50

ADD TO CART

Qty 1-9
€59,50
Qty 10+
€53,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
5.00 ±0.025

Back Focal Length BFL (mm):

14.33
Effective Focal Length EFL (mm): 15.00
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.58
Radius R ₁ =R ₂ (mm): 15.16
Clear Aperture CA (mm): 4.50
f/#: 3.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Numerical Aperture NA: 0.17
Type: Double-Convex Lens
Wavelength Range (nm): 750 - 1550
Damage Threshold, By Design: ☐ 8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View