

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 532nm ZX - 8X Research-Grade Variable Beam Expander



Research-Grade Variable Beam Expanders



Stock #87-567 CLEARANCE 3-4 DAYS

- 1 +

€1.645,00

ADD TO CART

Qty 1-4

€1.645,00

Qty 5+

€1.455,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0 ±0.06

Coating:

Laser V-Coat (532nm)
Design Wavelength DWL (nm): 532
Entrance Aperture (mm): 15
Exit Aperture (mm): 30
Expansion Power: 2X - 8X
Substrate: ☐ Fused Silica (Corning 7980)
Length (mm): 169.00
Mounting Threads: Input: Male C-Thread (1" x 32 TPI) Output: Male T-Thread (M42 x 0.75)
Transmission (%): >97.5 @ DWL
Type: Beam Expander
Weight (g): 501
Housing Diameter (mm): 51
Transmitted Wavefront, P-V: <λ/4 @ 532nm for Input Beam ≤4mm (2X-6X) <λ/4 @ 532nm for Input Beam ≤2mm (>6X)
Coating Specification: R _{abs} <0.25% @ 531 - 533nm R _{avg} <0.5% @ 510 - 555nm
Wavelength Range (nm): 510 - 555
Style: Variable Magnification
Damage Threshold, By Design: ☐ 5 J/cm ² (>3X), 3 J/cm ² (2-3X) @ 10ns, 20 Hz, 532nm
Divergence Adjustment: Non-Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View