


[See all 8 Products in Family](#)

5.7mm² DUV Photodiode with Metal Housing



DUVPhotodiodes

Stock **#84-981** [CONTACT US](#)

1 €90.⁰⁰

[ADD TO CART](#)

Volume Pricing

Qty 1-4	€90,00 each
Qty 5-9	€79,00 each
Qty 10-24	€70,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Rise Time (µs):
0.2 @ 0 V, 1 kΩ

Physical & Mechanical Properties

Size of Active Area (mm):
2.4 x 2.4

Active Area (mm²):

Optical Properties

980.00 **Peak Response Wavelength (nm):**

Electrical

0.5 **Responsivity @ 980nm (AW):**

Minimum: 0.3
Typical: 1 **Shunt Resistance @ V=-10mV (GΩ):**

0.34 **Responsivity @ 633nm (AW):**

0.12 **Responsivity @ 200nm (AW):**

65.00 **Capacitance @ V_R=0V (pF):**

3.6×10^{-14} **Noise Equivalent Power NEP (W/ Hz^{1/2}):**
@ 0 V, 200nm

5.00 **Maximum Reverse Voltage (V):**

Hardware & Interface Connectivity

TO-5 **Connector:**

Environmental & Durability Factors

-20 to +60 **Operating Temperature (°C):**

-55 to +80 **Storage Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Excellent UV Sensitivity
- High Shunt Resistance
- Low Capacitance

DUV Photodiodes are ideal for a wide variety of applications, including UV spectrophotometry and analytical and medical instrumentation. DUV Photodiodes are designed for enhanced responsivity from 200 – 400nm, and with sensitivity extending down to 190nm. DUV Photodiodes feature quartz windows and either metal or ceramic housing. Models with suppressed NIR performance are also available.