


TECHSPEC® 5mm Diameter x 1.75mm Thickness, NIR Coated, BOROFLOAT® Window

See More by [SCHOTT Optical Components](#)



TECHSPEC BOROFLOAT Borosilicate Windows

Stock #12-184 14 In Stock

-

1

+

€36^{.31}

ADD TO CART

Volume Pricing	
Qty 1-5	€36,31 each
Qty 6-25	€29,10 each
Qty 26-99	€26,52 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Protective Window

Physical & Mechanical Properties	
Protective as needed	Bevel:
≥90	Clear Aperture (%):
4.50	Clear Aperture CA (mm):
5.00 ±0.5	Diameter (mm):
1.75 ±0.2	Thickness (mm):
Ground	Edges:
480.00	Knoop Hardness (kg/mm²):
0.20	Poisson's Ratio:
64	Young's Modulus (GPa):
Optical Properties	
65.41	Abbe Number (v _d):
NIR (700-1150nm)	Coating:
R _{avg} <1.0% @ 700 - 1150nm	Coating Specification:
1.472	Index of Refraction (n _d):
BOROFLOAT®	Substrate:
4 - 6λ	Surface Flatness (P-V):
80-50	Surface Quality:
≥97	Transmission (%):
700 - 1150	Wavelength Range (nm):
Material Properties	
3.25 (+20 to +300°C)	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
2.23	Density (g/cm³):
525	Transformation Temperature (°C):
Environmental & Durability Factors	
1 hour @ 500; >100 hours @ 450	Operating Temperature (°C):
Short Term, 1 hr: 110K 1 - 100 hrs: 90K Long Term, >100 hrs: 80K	Resistance to Temperature Difference (K):
Up to 4mm Thick: 175K 4 - 6mm Thick: 160K 6 - 15mm Thick: 150K	Thermal Shock (K):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:


PRODUCT DETAILS

- Low Coefficient of Thermal Expansion
- Visible to Near Infrared Transmission
- High Resistance to Thermal Shock

TECHSPEC® BOROFLOAT® Borosilicate Windows are ideal for high temperature and harsh environment applications. The windows have a low coefficient of thermal expansion of 3.25 (+20 to +300°C). TECHSPEC® BOROFLOAT® Borosilicate Windows feature visible to near infrared transmission. Unlike common borosilicate that is drawn flat, BOROFLOAT® is produced by a float technique that yields superior surface flatness — typically 4 - 6λ per inch. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass.

Can't find what you need? Get a quick [custom quote](#).

TECHNICAL INFORMATION



QUOTE YOUR SIZE

COMPATIBLE MOUNTS