

**TECHSPEC® 5mm FL f/4, Blue Series IR-Cut M12 Lens**



Stock #24-443 **6 In Stock**

⊖ 1 ⊕ €80<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-49	€80,00 each
Qty 50+	€64,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Blue Series **Product Family:**

M12 Imaging Lens **Type:**

Yes **IR Cut Filter:**

IR-Cut Filter      Special Type of Lens:

## Physical & Mechanical Properties

Fixed      Iris Option:  
14.60      Length (mm):  
14      Maximum Diameter (mm):  
14      Outer Diameter (mm):  
4      Weight (g):

## Optical Properties

Horizontal Field of View @ Max Sensor Format:  
57.3°

Field of View at Max Sensor Format:  
Horizontal: 165.7mm - 57.3°  
Vertical: 117.5mm - 42.3°  
Diagonal: 225.4mm - 73.4°

Horizontal Field of View, 1/3" Sensor:  
165.6mm - 57.3°

Horizontal Field of View, 1/4" Sensor:  
117.5mm - 42.3°

6.00      Maximum Image Circle (mm):

0.0040      Numerical Aperture NA, Object Side:

6(5)      Number of Elements (Groups):

400 - 700      Wavelength Range (nm):

5.00      Focal Length FL (mm):

150 - ∞      Working Distance (mm):

f/4      Aperture (f#):

-18.88 @ Full Field      Distortion (%):

4.0 - 3.9      Back Focal Length BFL (mm):

M4 MgF<sub>2</sub> @ 550nm      Coating Specification:

2.74      Entrance Pupil Position (mm):

5.94      Object Space Principal Plane (mm):

2.53      Image Space Principal Plane (mm):

-18.88      Maximum Distortion (%):

-6.51      Exit Pupil Position (mm):

VS (IR-Cut Filter)      Lens Wavelength Range:

## Sensor

1/3"      Maximum Sensor Format:

1.40      Pixel Size (μm):

## Threading & Mounting

N/A      Filter Thread:

S-Mount (M12 x 0.5)      Mount:

## Regulatory Compliance

Compliant      RoHS 2015:

## Product Details

- Up to 1/2", S-Mount Lens
- Up to 5 MegaPixels, 1.4µm Pixel Size Sensors
- High Resolution Board Camera Lens Optimized for Close WD
- 2mm to 35mm Focal Length
- [Ruggedized Designs](#) Also Available

TECHSPEC® Blue Series M12 Lenses feature high resolution performance, along with the same great versatility of our [TECHSPEC® Green Series M12 Lenses](#). Each lens consists of several precision glass elements mounted in a compact, aluminum housing. These lenses can connect to C-Mount cameras using the M12 x0.5 Adapter for C-Mount Cameras ([#53-675](#)) or the M12 x0.5 C-Mount Adapter with Rubber O-Ring ([#59-241](#)) for vibration-sensitive environments. TECHSPEC® Blue Series M12 Lenses are ideal for automotive, industrial, and medical imaging application. Prescription data is available by submitting a [Request for Prescription Form](#).

**Note:** Compatible [TECHSPEC® M12 Imaging Lens Accessories](#) available.

Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- **Blue Series M12 Lenses:** High resolution finite conjugate designs optimized for machine vision working distances.
- **Rugged Blue Series M12 Lenses:** [Stabilized ruggedization](#) versions of our Blue Series M12 Lenses, utilizing the same optics.
- **Green Series M12 Lenses:** Finite conjugate designs optimized for machine vision working distances.
- **Red Series M12 Lenses:** Infinite conjugate designs optimized for high resolution performance out to infinity.
- **HEO Series M12 Lenses:** Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- **Liquid Lens M12 Lenses:** Integrated liquid lens for fast electronic focus.

## Technical Information

Focal Length	A	B	C*	D
2.0mm	18.0mm	21.7mm	2.26mm	4.75mm
3.0mm	14.0mm	17.1mm	4.8 - 4.7mm	5.8mm
4.0mm	14.0mm	19.7mm	6.1 - 6.0mm	4.4mm
5.0mm	14.0mm	14.6mm	4.0 - 3.9mm	3.7mm
6.0mm	14.0mm	14.1mm	6.9 - 6.8mm	4.5mm
8.0mm	14.0mm	12.3mm	8.8 - 8.6mm	3.7mm
10.0mm	14.0mm	17.0mm	6.6 - 6.3mm	3.7mm
12.5mm	15.0mm	22.9mm	10.1 - 9.7mm	4.8mm
17.5mm	14.0mm	20.7mm	5.8 - 4.9mm	7.6mm
25.0mm	18.0mm	30.0mm	8.5 - 6.5mm	11.5mm
35.0mm	18.0mm	29.5mm	18.72 - 14.0mm	14.5mm

\*Specified for Optimized Working Distance of 150 - 250mm.