


[See all 60 Products in Family](#)

## TECHSPEC® 6" Dia, 24" FL 750-1100nm, Spherical Mirror



Stock #73-036 [CONTACT US](#)

⊖ 1 ⊕ €1.220<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€1.220,00 each
Qty 6-24	€976,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Spherical Mirror **Type:**

### Physical & Mechanical Properties

152.40 +1.5/-0 **Diameter (mm):**

Ground	<b>Back Surface:</b>
6.0	<b>Diameter (inches):</b>
+0.06/-0	<b>Diameter Tolerance (inches):</b>
1.00	<b>Edge Thickness ET (inches):</b>
25.40	<b>Edge Thickness ET (mm):</b>
+0.0/-15	<b>Edge Thickness Tolerance (%):</b>

## Optical Properties

Dielectric	<b>Coating Type:</b>
Dielectric Mirror (750-1100nm)	<b>Coating:</b>
750 - 1100	<b>Wavelength Range (nm):</b>
609.60	<b>Effective Focal Length EFL (mm):</b>
BOROFLOAT® SUPREMAX®	<b>Substrate:</b> <input type="checkbox"/>
f/4	<b>Aperture (f/#):</b>
R <sub>avg</sub> >98% @ 750 - 1100nm (0 - 45°) R <sub>avg</sub> >99% @ 750 - 1100nm (0°)	<b>Coating Specification:</b>
24.00	<b>Effective Focal Length EFL (inches):</b>
±2	<b>Focal Length Tolerance (%):</b>
M4	<b>Surface Accuracy:</b>
60-40	<b>Surface Quality:</b>
1 J/cm <sup>2</sup> @ 1064nm, 20ns, 20Hz	<b>Damage Threshold, By Design:</b> <input type="checkbox"/>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------


## Product Details

- Ideal for Multispectral Focusing Applications
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Multiple Sizes Available


TECHSPEC® Broadband Dielectric Spherical Mirrors are ideal for light collection in multispectral imaging applications. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. BOROFLOAT® substrate provides a good combination of performance and value. TECHSPEC® Broadband Dielectric Spherical Mirrors are available in diameters ranging from 25.4 to 152.4mm for ease of system integration. These mirrors collect and focus light without introducing chromatic aberration.

## Technical Information

### UV



### VIS



### NIR

