

6" x 6" Laser Safety Barrier



Laser Safety Barriers

Stock **#14-730** **1 In Stock**

-

1

+

€63^{.50}

ADD TO CART

Volume Pricing	
Qty 1-3	€63,50 each
Qty 4+	€56,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Included Hardware:

- (2) ¼-20, 1/2" Long SHCS
- (2) M6 x 1.0, 10mm Long SHCS
- (1) English Allen Wrench ([#55-192](#))
- (1) Metric Allen Wrench ([#55-200](#))

Straight Wall		Style:
Physical & Mechanical Properties		
Construction:		Bead-Blasted Anodized Aluminum
Dimensions (inches):		6 x 6
Dimensions (mm):		152.4 x 152.4
Thickness (mm):		2.00
Through Hole Length (mm):		50.80
Through Hole Orientation:		2 x Holes Centered on Mounting Lip
Through Hole Diameter (mm):		7
Base Width (mm):		20
Regulatory Compliance		
Certificate of Conformance:		View

PRODUCT DETAILS

- Safely Isolate Laser Experiment
- Compatible with 1/4-20 and M6 x 1.0 Breadboards and Tables
- Anodized Aluminum Construction

Laser Safety Barriers provide protection from exposure to harmful laser radiation in benchtop systems. These barriers are designed to separate multiple experiments on a single table or to shield an area from debris that can damage sensitive optical components. Manufactured from anodized aluminum, these protective plates are available in various sizes with a standard 2mm thickness, and are compatible with both Metric and English threaded lab tables and benches. Laser Safety Barriers have a 20mm mounting lip and include all necessary mounting screws and hardware for assembly.

Note: Laser Safety Barriers should never be used as a replacement for Laser Safety Eyewear or any other forms of personal protective equipment (PPE). These are intended to be used along with any other forms of PPE your workspace or laboratory requires.