


[See all 19 Products in Family](#)

6 x 6 x 0.2mm, 800nm THG, Type I BBO Nonlinear Crystal



Mounted Type I BBO Nonlinear Crystal

Stock #11-170 **3 In Stock**

⊖ 1 ⊕ €623⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-2	€623,00 each
Qty 3+	€545,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Nonlinear Crystal

Type:

THG @ 800nm, Type I

Typical Applications:

Note:
Mount is 25.4mm Dia., 6mm Thick Unthreaded Black Anodized Metal Mount (see drawing for more information)

BBO	Crystal Type:
<0.1mm x45°	Protective Chamfer:
Physical & Mechanical Properties	
6.0 x6.0 +0.0/-0.1	Dimensions (mm):
0.20 +0.0/-0.1	Thickness (mm):
5.70	Clear Aperture CA (mm):
<20	Parallelism (arcsec):
<5	Perpendicularity (arcmin):
Optical Properties	
20-10	Surface Quality:
AR Coating	Coating:
800	Design Wavelength DWL (nm):
$\lambda/8$	Surface Flatness (P-V):
Coating Specification: S1: 400 - 800nm Protective Coating S2: 266nm Protective Coating	
Damage Threshold, By Design: <input type="checkbox"/> 10 J/cm ² @ 1064nm, 10ns, 10Hz	
Damage Threshold, Pulsed: 10 J/cm ² @ 1064nm, 10ns, 10Hz	
44.3/90	Orientation Θ/Φ (°):
Threading & Mounting	
Mounted	Mount:
6 (unthreaded)	Mount Thickness (mm):
25.4	Mount Diameter (mm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- BBO Crystals for Frequency Conversion of 800nm and 1030nm Lasers
- LBO Crystals for Frequency Conversion of 1030nm and 1064nm Lasers
- High Damage Thresholds Up to 10 J/cm² @ 1064nm, 10ns, 10Hz
- Broad Transparency Range from the UV to the IR

Nonlinear Crystals of either β -barium borate (BBO) or lithium triborate (LBO) are used for frequency conversion of laser sources. BBO crystals feature thicknesses from 0.2mm to 0.5mm to minimize group velocity mismatch and are ideal for frequency doubling or tripling of Ti:Sapphire and Yb:doped laser pulses. The critical and noncritical phase matching LBO crystals are ideal for second or third harmonic generation of Nd:YAG and Yb:doped lasers. Nonlinear Crystals with 20-10 surface quality and $\lambda/10$ (LBO) or $\lambda/8$ (BBO) surface flatness provide the broad transparency range and large nonlinear coefficient needed for the harmonic generation of fundamental laser frequencies. Each crystal features a protective anti-reflection (AR) coating that minimizes reflection and limits fogging from ambient conditions.