

TECHSPEC<sup>®</sup> 5mm Dia. x 25mm FL, VIS 0° Inked, Double-Convex Lens



Stock #63-598-INK

CONTACT US

☐ Other Coating Options

-

1

+

€68<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | €68,00 each                   |
| Qty 10-24      | €61,50 each                   |
| Qty 25-99      | €54,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Double-Convex Lens

Physical & Mechanical Properties

|                                      |                                                       |
|--------------------------------------|-------------------------------------------------------|
| 5.00 ±0.025                          | Diameter (mm):                                        |
| <1                                   | Centering (arcmin):                                   |
| Protective as needed                 | Bevel:                                                |
| 1.50                                 | Center Thickness CT (mm):                             |
| ±0.05                                | Center Thickness Tolerance (mm):                      |
| 1.26                                 | Edge Thickness ET (mm):                               |
| 4.5                                  | Clear Aperture CA (mm):                               |
| Optical Properties                   |                                                       |
| 24.50                                | Back Focal Length BFL (mm):                           |
| 25.00                                | Effective Focal Length EFL (mm):                      |
| VIS 0° (425-675nm)                   | Coating:                                              |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm | Coating Specification:                                |
| N-BK7                                | Substrate: <input type="checkbox"/>                   |
| 40-20                                | Surface Quality:                                      |
| 1.5λ                                 | Power (P-V) @ 632.8nm:                                |
| λ/4                                  | Irregularity (P-V) @ 632.8nm:                         |
| 25.58                                | Radius R <sub>1</sub> =R <sub>2</sub> (mm):           |
| 5.00                                 | f/#:                                                  |
| 587.6                                | Focal Length Specification Wavelength (nm):           |
| ±1                                   | Focal Length Tolerance (%):                           |
| 0.10                                 | Numerical Aperture NA:                                |
| 425 - 675                            | Wavelength Range (nm):                                |
| 5 J/cm² @ 532nm, 10ns                | Damage Threshold, By Design: <input type="checkbox"/> |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| View                  | Certificate of Conformance: |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- AR Coated to Provide <0.4% Reflectance per Surface for 425 - 675nm
- Minimize Aberrations Including Spherical and Coma
- [UV Fused Silica DCX Lenses](#) Available
- Other Coating Options Available: [Uncoated](#), [MgF<sub>2</sub>](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), [VIS-NIR](#), and [YAG-BBAR](#)


TECHSPEC® VIS 0° Coated Double-Convex (DCX) Lenses, also referred to as bi-convex lenses, have two positive, symmetrical faces with equal radii on both sides. These lenses are generally recommended for finite imaging applications with a conjugate ratio (ratio between object distance and image distance) between 0.2 and 5. At a conjugate ratio of 1, aberrations such as spherical aberration, chromatic aberration, coma, and distortion are minimized or cancelled due to the symmetric lens design. TECHSPEC® VIS 0° Coated Double-Convex Lenses are available in a variety of substrates and coating options for the visible and NIR spectra.

Technical Information



N-BK7


Uncoated N-BK7 Typical Transmission



Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.

[Click Here to Download Data](#)

N-BK7 with MgF<sub>2</sub> Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$  (N-BK7)

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-NIR Coating Typical Transmission








Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 0.25\% @ 880\text{nm}$   
 $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$   
 $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

|                                                                                                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                                            | <a href="#">Click Here to Download Data</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| <p data-bbox="596 270 974 359"><b>N-BK7 with VIS 0° Coating</b><br/><b>Typical Transmission</b></p>       | <p data-bbox="1337 403 1843 451">Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p data-bbox="1337 465 1850 513">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1478 528 1709 552"><math>R_{avg} \leq 0.4\%</math> @ 425 - 675nm</p> <p data-bbox="1341 566 1841 614">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1474 629 1709 652"><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                          |
| <p data-bbox="569 863 1037 952"><b>N-BK7 with YAG-BBAR Coating</b><br/><b>Typical Transmission</b></p>   | <p data-bbox="1341 997 1841 1044">Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p data-bbox="1333 1059 1850 1107">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1493 1121 1688 1145"><math>R_{abs} \leq 0.25\%</math> @ 532nm</p> <p data-bbox="1493 1145 1688 1169"><math>R_{abs} \leq 0.25\%</math> @ 1064nm</p> <p data-bbox="1472 1169 1709 1193"><math>R_{avg} \leq 1.0\%</math> @ 500 - 1100nm</p> <p data-bbox="1341 1207 1841 1255">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1474 1270 1709 1294"><a href="#">Click Here to Download Data</a></p>            |
| <p data-bbox="617 1492 1008 1581"><b>N-BK7 with NIR I Coating</b><br/><b>Typical Transmission</b></p>   | <p data-bbox="1341 1656 1841 1703">Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.</p> <p data-bbox="1333 1718 1850 1765">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1472 1780 1709 1804"><math>R_{avg} \leq 0.5\%</math> @ 600 - 1050nm</p> <p data-bbox="1341 1819 1841 1866">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1474 1881 1709 1905"><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                             |
| <p data-bbox="606 2139 1016 2228"><b>N-BK7 with NIR II Coating</b><br/><b>Typical Transmission</b></p>  | <p data-bbox="1341 2264 1841 2312">Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.</p> <p data-bbox="1333 2326 1850 2374">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1478 2389 1703 2412"><math>R_{abs} \leq 1.5\%</math> @ 750 - 800nm</p> <p data-bbox="1478 2412 1703 2436"><math>R_{abs} \leq 1.0\%</math> @ 800 - 1550nm</p> <p data-bbox="1472 2436 1709 2460"><math>R_{avg} \leq 0.7\%</math> @ 750 - 1550nm</p> <p data-bbox="1341 2499 1841 2546">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1474 2561 1709 2585"><a href="#">Click Here to Download Data</a></p> |

Coating Curves

Compatible Mounts

---

;