

Coherent® StingRay™ Projection Head 1254120 | 514nm, 60° Fan

See More by [Coherent®](#)



60° Line, 514nm Stingray Projection Head, #89-579

Stock **#89-579** 1 In Stock

-

1

+

€348^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€348,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads



General

Type:

1 Line

Compatible Laser Models:

[86-848](#), [87-522](#)

Manufacturer:

Coherent®

Optical Properties

514.00	Wavelength (nm):
Green	Color:
60.00	Fan Angle (°):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- [Coherent® StingRay™ Developer's Kit](#) also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

Note: For CDRH certified systems (Class IIIb), [#86-878](#) Laser Controller and additional external voltage source (0.5–5V) with BNC connector is required.