


**TECHSPEC® 600nm, 12.5 x 17.6mm, Dichroic Longpass Filter**



Stock **#69-879** 3-4 DAYS

⊖ 1 ⊕ **€123,00**

ADD TO CART

|         |
|---------|
| Qty 1-5 |
| €123,00 |

|        |
|--------|
| Qty 6+ |
| €98,50 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Dimensions (mm):**  
12.5 x 17.6

**Angle of Incidence (°):**  
45

**Cut-On Wavelength (nm):**  
600.00

|                                                                                                                                                                                                           |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div>Substrate: <div><div></div></div><div>Fused Silica (Coming 7980)</div></div>                                                                                                                         |
| <div>Length (mm):<div>17.60</div></div>                                                                                                                                                                   |
| <div>Coating:<div>Hard Coated</div></div>                                                                                                                                                                 |
| <div>Reflection (%):<div>&gt;97, Average Polarization</div><div>&gt;95, Absolute Polarization</div></div>                                                                                                 |
| <div>Reflection Wavelength (nm):<div>460 - 570</div></div>                                                                                                                                                |
| <div>Surface Quality:<div>60-40</div></div>                                                                                                                                                               |
| <div>Thickness (mm):<div>1.05</div></div>                                                                                                                                                                 |
| <div>Thickness Tolerance (mm):<div>±0.1</div></div>                                                                                                                                                       |
| <div>Transmission (%):<div>&gt;85, Average Polarization</div><div>&gt;80, Absolute Polarization</div></div>                                                                                               |
| <div>Transmission Wavelength (nm):<div>625 - 1600</div></div>                                                                                                                                             |
| <div>Type:<div>Dichroic Filter</div></div>                                                                                                                                                                |
| <div>Width (mm):<div>12.50</div></div>                                                                                                                                                                    |
| <div>Dimensional Tolerance (mm):<div>+0.0/-0.2</div></div>                                                                                                                                                |
| <div>Transmitted Wavefront Tolerance:<div>λ/4</div></div>                                                                                                                                                 |
| <div>Cut-On Tolerance (%):<div>±2</div></div>                                                                                                                                                             |
| <div>Slope Factor (%):<div>3.00</div></div>                                                                                                                                                               |
| <div>Environmental Durability:<div>Humidity per ML-STD-810H, Section 507.6</div><div>Temperature per ML-STD-810H, Section 501.7 and 502.7</div></div>                                                     |
| <div>Physical Durability:<div>Adhesion per ML-PRF-13830B, Section C.4.5.12</div><div>Moderate abrasion per ML-PRF-13830B, Section C.4.5.11</div><div>Cleaning per ML-C-48497A Section 4.5.4.2</div></div> |
| <div>Wavelength Range (nm):<div>460 - 1600</div></div>                                                                                                                                                    |
| <div>Wavelength Range (μm):<div>0.46 - 1.6</div></div>                                                                                                                                                    |

## Regulatory Compliance

|                                                       |
|-------------------------------------------------------|
| <div>RoHS 2015:<div>Compliant</div></div>             |
| <div>Certificate of Conformance:<div>View</div></div> |
| <div>Reach 240:<div>Compliant</div></div>             |