

60mm Center of Rotation, Motorized Goniometer Stage, Integrated Controller with Encoder

See More by [Zaber™](#)



Stock **#26-078** **1 In Stock**

-

1

+

€3.028²⁰

ADD TO CART

Volume Pricing	
Qty 1+	€3.028,20 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

SPECIFICATIONS

General

Metric

Type:

Yes	Encoder:
Yes	Manual Control:
Note: Requires a 24-48 VDC power supply and either #15-295 for USB connectivity or #15-297 for RS-232 connectivity. A data cable (#15-296 or #15-299) can be used to daisy chain multiple stages together to control simultaneously.	
2-Phase Stepper	Type of Motor:
Rotary Quadrature Encoder	Encoder Type:

Physical & Mechanical Properties

Goniometer	Type of Movement:
Crossed Roller Bearing	Guide System:
40 x 40	Stage Size (mm):
±7	Travel (°):
0.06, Unidirectional	Accuracy (°):
< 0.01	Backlash (°):
20.8	Height (mm):
3	Load Capacity (kg):
30 (Centered Load)	Load Capacity (N):
60	Radius R (mm):
< 0.005	Repeatability (°):
1.975	Resolution (μrad):
Max: 30	Speed (°/s):
0.285	Weight (kg):
200 CPR	Encoder Resolution:

Electrical

350	Current (mA):
-----	---------------

Hardware & Interface Connectivity

Precision Worm Gear	Type of Drive:
Power Supply: Power Supply Required and Sold Separately. USA: #15-294 Europe: #15-294 Japan: #23-662 Korea: #33-773 China: #15-294	
USB with #15-295 RS-232 with #15-297	Computer Interface:

Environmental & Durability Factors

0 to +50	Operating Temperature (°C):
----------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- 40mm and 60mm Center of Rotation Options
- Vacuum-Compatible Options
- Small Footprint with a Low Profile for Compact Systems
- 30N (~3kg) Centered Load Capacity
- Available with Integrated, 200 Counts per Revolution (CPR) Motor Mounted Encoder

Zaber™ Motorized Goniometers provide electronically controlled, precise angular adjustment of an object about a fixed point located above the center of the mounting surface. Featuring a built-in controller, these goniometers can be controlled manually with an indexed control knob or computer controlled via RS-232 communication or via USB with the included software. Encoder version are available for all travel options, with 200 Counts per Revolution (CPR) rotary quadrature encoders integrated into the stepper motor. Zaber™ Motorized Goniometers are ideal for providing tip and tilt adjustment for optical components in laser alignment and beam steering applications. These goniometers feature an interlocking alignment system to ensure a common center of rotation when the 40mm and 60mm options are stacked, and can be daisy-chained with additional stages using only one power supply for ease of system integration.

Note: A 24-48 VDC universal power supply, data cables for daisy chaining, and computer interface cables (USB or RS-232) are sold separately as accessories.
