

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 6.25mm Dia. x 15mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock #32-301 3-4 DAYS

[Other Coating Options](#)

1 €63,00

ADD TO CART

Qty 1-5

€63,00

Qty 6+

€50,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.025

Effective Focal Length EFL (mm): 15.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 12.73
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 5.625
Centering (arcmin): <1
Center Thickness CT (mm): 3.30 ±0.10
Center Thickness CT 1 (mm): 2.70 ±0.05
Center Thickness CT 2 (mm): 0.60 ±0.05
Radius R₁ (mm): 7.95
Radius R₂ (mm): -7.25
Radius R₃ (mm): -277.83
Edge Thickness ET (mm): 2.64
Substrate: N-SSK3 / N-SF10
Surface Quality: 40-20
f/#: 2.4
Numerical Aperture NA: 0.21
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View