

630nm LED Area Light



Stock **#63-308** CLEARANCE **5 In Stock**

-

1

+

€474^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€474,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
100,000	LED Lifetime (hours):
228.00	Irradiance at 100mm (W/m²):
LED Illuminator	Type of Illumination:
Area Light	Geometry:
	Illumination Mode:

Strobed or Constant	
Physical & Mechanical Properties	
Diameter (mm):	35.00
Height (mm):	29.5
Optical Properties	
Color:	Red
Full Width-Half Max FWHM (nm):	30.00
Wavelength (nm):	630
Divergence Angle (°):	±9.2
Spot Size at 100mm Working Distance (mm):	45.00
Hardware & Interface Connectivity	
Power Supply:	Power Supply Required and Sold Separately. USA: #59-433 Europe: Not Available Japan: #59-433 Korea: Not Available China: #59-433

Regulatory Compliance	
RoHS 2015:	Compliant
Reach 209:	Compliant
Certificate of Conformance:	View

Product Details


[#59-433](#) Universal Power Supply is required for operation. [#59-371](#) DC Current Controller is required for UV area lights. [#63-342](#) Area and Spot Light Heat Sink is recommended to maintain performance and optimize product lifetime.


- Variable Intensity with DC Current Controller
- Excellent Uniformity
- 100,000 Hour Product Lifetime
- [Heat Sinks and Power Supplies](#) Sold Separately

Compact LED Area Lights provide the high-power illumination required in machine vision, biomedical, fluorescence, and strobing applications. Each LED module contains four M3 mounting holes on a 29mm diameter circle. The universal power supply, which accepts a 90 - 245V AC input, ships with clip-on adapters for the US, Europe, and UK. Through the DIN rail mountable DC current controller, LED intensity can be adjusted manually via a potentiometer or by supplying a 0 - 5V analog control input. The DC current controller is designed to deliver up to 400mA at 24V.

Note: [#59-433](#) Universal Power Supply is required for operation. [#59-371](#) DC Current Controller is required for UV area lights. [#63-342](#) Area and Spot Light Heat Sink is recommended to maintain performance and optimize product lifetime.

Technical Information





;