

TECHSPEC® 6.0mm Dia. x 6.0mm FL, NIR I, Inked, Plano-Convex Lens



Stock **#48-714-INK** ☐ In Stock
[Other Coating Options](#)

1 **€48,50**

ADD TO CART

Qty 1-9
€48,50
Qty 10+
€43,75
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 ±0.025

Effective Focal Length EFL (mm):

6.00 @ 587.6nm
Back Focal Length BFL (mm): 4.60
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 2.50 ±0.05
Edge Thickness ET (mm): 1.42
Radius R₁ (mm): 4.71
Clear Aperture CA (mm): 5.4
f/#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View