

[All Products](#) / [Laser Optics](#) / [Laser Optics](#) / [405nm Laser Line Coated Plano-Convex](#)


[See all 102 Products in Family](#)

TECHSPEC® 6.0mm

6.0mm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit

Options

1

€50^{,50}

ADD TO CART

Volume Pricing

Qty 1-9 €50,50 each

Qty 10-25 €45,50 each

Qty 26-49 €40,50 each

Need More? [Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Product Downloads

- STEP:stp
- Curve:pdf
- PDF Drawing:pdf
- ISO 10110 Drawing
- IGES:igs
- Zemax:zar
- Zemax:zip
- Zemax:zmx
- eDrawing:eprt
- Code V:seq
- EO Spec Sheet
- [Download All](#)

General

Type: Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm): 6.00 +0.0/-0.025

Centering (arcmin): <3

Center Thickness CT (mm): 2.50 ±0.05

Edge Thickness ET (mm): 1.68

Clear Aperture CA (mm): 5.4

Bevel: Protective as needed

Optical Properties

Effective Focal Length EFL (mm): 7.50 @ 587.6nm

Back Focal Length BFL (mm): 6.1

Coating: Laser V-Coat (405nm)

Coating Specification: R_{abs} <0.25% @ 405nm

Substrate: [N-SF11](#)

Surface Quality: 40-20

Power (P-V) @ 632.8nm: 1.5λ

Irregularity (P-V) @ 632.8nm: λ/4

Focal Length Tolerance (%): ±1

Radius R₁ (mm): 5.89

f/#: 1.25

Numerical Aperture NA: 0.40

Design 405
Wavelength
DWL (nm):

Damage 3 J/cm² @
Threshold, By 405nm, 10ns
Design: ⓘ

Regulatory Compliance

RoHS 2015: **Compliant**

Reach 235: **Compliant**

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- <0.25% Reflection at 405nm for Diode Applications
- BBAR Coating Options Also Available: [uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
- 405nm, [532nm](#), [633nm](#), [785nm](#), [980nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

TECHSPEC® 405nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC® 405nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: [532nm](#), [633nm](#), [785nm](#), [980nm](#), [1064nm](#), and [1550nm](#). Other coating options are available, including [uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#).

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)

Technical Information

Related Products











#13-800 - Small Lens Clamp for 4-8mm Dia. Optics
€172,00

Qty



Compatible Mounts

	Title	Type	Compare	Stock Number	Price	Buy
MORE+ 	6.0mm Optic Dia., Optic Mount				€32,75	2 In Stock <input type="text" value="1"/> 
MORE+ 	6mm Diameter, Mount Thin Optic Mou					20+ In Stock <input type="text" value="1"/> 
MORE+ 	6mm Inner Single Optic Mount	Fixed		#38-745	€41,00 Request Quote	20+ In Stock <input type="text" value="1"/> 
MORE+ 	6mm Diameter, C-Mount Thin Optic Mount	Fixed		#54-613	€59,50 Request Quote	10 In Stock <input type="text" value="1"/> 

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Check out our full selection of mounts [here](#).

Resources

Media Type

- Application Note
- Technical Tool
- Video
- FAQ
- Trending in Optics
- Glossary
- Scientific Paper
- Published Article

APPLICATION NOTE

An Introduction to Optical Coatings

TECHNICAL TOOL

Gaussian Beams Calculator

VIDEO

Polarization Directed Flat Lenses Product Review

FAQ

What is the best lens for focusing or collimating th...

TRENDING IN OPTICS

Free-Space Optical Communication

APPLICATION NOTE

Common Laser Optics Materials

[View More](#)