

[See all 25 Products in Family](#)

690nm Single Stage Free-Space Optical Isolator



405nm Single Stage Free-Space Optical Isolator, #35-969



Stock **#35-971** **1 In Stock**

- 1 + €4.135⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	€4.135,00 each
Qty 5+	€3.725,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Single Stage Optical Isolator

Type:

Faraday

Style:

Physical & Mechanical Properties

4.7 Clear Aperture CA (mm):

Optical Properties

>85 Minimum Transmission (%):

92 Transmission (%):

690 Design Wavelength DWL (nm):

670 - 710 Wavelength Range (nm):

40 W, 4 kW/cm² @ DWL Damage Threshold, By Design:

43 Typical Isolation at Design Wavelength (dB):

>35 Minimum Isolation at Design Wavelength (dB):

Environmental & Durability Factors

+15 to +40 Operating Temperature (°C):

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Up to 67 dB Isolation for Ultimate Stability
- Up to 92% Transmission for Maximum Power
- 4.7mm Input Aperture

Free-Space Optical Isolators incorporate a Faraday Rotator and are specifically designed and manufactured to provide superior performance with high isolation, transmission, and power densities. Each option effectively reduces feedback in the external cavity of diode laser systems and blocks reflections from free-space fiber coupling. Free-Space Optical Isolators increase power stabilization in optical systems and also eliminate feedback-induced damage to sensitive optical components. These isolators enable state of the art protection for the most stable lasers in the world and are ideal for demanding laser applications.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)