

60mm Motorized Rotary Stage

See More by [Zaber™](#)



60mm Motorized Rotary Stage, #15-291

Stock **#15-291** 3-4 DAYS

-

1

+

€2.550,00

ADD TO CART

Qty 1+
€2.550,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Rotary

Type of Drive:
Stepping Motor

Type:
Universal (Metric & English)

Stage Size (mm):
82.6 x 144.8

Travel (°): 360
Accuracy (°): 0.08, Unidirectional
Backlash (°): <0.04
Center Hole: 23mm Clear Aperture to hold a 25mm (1") Dia. Optic (up to 3mm Thick)
Load Capacity (kg): 20
Model Number: Zaber X-RSW60A
Note: Requires a 24-48 VDC power supply and either #15-295 for USB connectivity or #15-297 for RS-232 connectivity. A data cable (#15-296 or #15-299) can be used to daisy chain multiple stages together to control simultaneously.
Operating Temperature (°C): 0 - 50
Power Supply: Power Supply Required and Sold Separately. USA: #15-294 Europe: #15-294 Japan: #15-302 Korea: #33-773 China: #15-294
Repeatability (°): <0.02
Speed (°/s): 0.0001 to 115
Weight (kg): 0.66
Computer Interface: USB with #15-295 RS-232 with #15-297
Maximum Operating Current (mA): 950
Table Diameter (mm): 60
Max. Continuous Torque (N⋅cm): 225

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant