

**TECHSPEC® 6mm Dia. x 15mm FL, NIR I Coated, Plano-Convex Lens**



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#18-115** 3-4 DAYS

⊖ 1 ⊕

**€130,00**

ADD TO CART

Qty 1-5

€130,00

Qty 6+

€104,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
6.00 -0.025

**Effective Focal Length EFL (mm):**

|                                                                                                                                                    |
|----------------------------------------------------------------------------------------------------------------------------------------------------|
| 15.00 @ 587.6nm                                                                                                                                    |
| <b>Back Focal Length BFL (mm):</b><br>13.63                                                                                                        |
| <b>Coating:</b><br>NIR I (600-1050nm)                                                                                                              |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.5% @ 600 - 1050nm                                                                             |
| <b>Substrate:</b> <br><a href="#">Fused Silica</a> (Corning 7980) |
| <b>Surface Quality:</b><br>40-20                                                                                                                   |
| <b>Power (P-V) @ 632.8nm:</b><br>3 Rings                                                                                                           |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>0.5 Rings                                                                                                  |
| <b>Focal Length Tolerance (%):</b><br>±1                                                                                                           |
| <b>Centering (arcmin):</b><br><1                                                                                                                   |
| <b>Center Thickness CT (mm):</b><br>2.00 ±0.05                                                                                                     |
| <b>Edge Thickness ET (mm):</b><br>1.31                                                                                                             |
| <b>Radius R<sub>1</sub> (mm):</b><br>6.88                                                                                                          |
| <b>Clear Aperture CA (mm):</b><br>5                                                                                                                |
| <b>f/#:</b><br>2.5                                                                                                                                 |
| <b>Numerical Aperture NA:</b><br>0.20                                                                                                              |
| <b>Type:</b><br>Plano-Convex Lens                                                                                                                  |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                                        |
| <b>Wavelength Range (nm):</b><br>600 - 1050                                                                                                        |
| <b>Damage Threshold, Reference:</b> <br>7 J/cm² @ 1064nm, 10ns  |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |