

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 6.25mm Dia. X 20mm FL, VIS-NIR, Inked, Achromatic Lens



Stock #49-306-INK 3-5 DAYS

[Other Coating Options](#)



1



€82,00

ADD TO CART

Qty 1-5

€82,00

Qty 6+

€65,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.25 ±0.025

Effective Focal Length EFL (mm):

20.00
Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 18.23
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 5.625
Centering (arcmin) : <1
Center Thickness CT (mm) : 3.60 ±0.10
Center Thickness CT 1 (mm) : 2.70 ±0.05
Center Thickness CT 2 (mm) : 0.90 ±0.05
Radius R₁ (mm) : 12.30
Radius R₂ (mm) : -8.71
Radius R₃ (mm) : -24.98
Edge Thickness ET (mm) : 3.00
Substrate:  N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 3.2
Numerical Aperture NA : 0.16
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
REACH 201 : Compliant
Certificate of Conformance : View