

## 632.8nm, 55mW Free Space Frequency Stabilized Laser Diode



632.8nm Frequency Stabilized Laser Diodes (Free Space and Fiber-Coupled options shown)

Stock **#33-045** **2 In Stock**

⊖ 1 ⊕ €6.900<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€6.900,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads



### General

2.00 **Warm-Up Time (minutes):**

1.5 - 2 (Output Beam) **Aspect Ratio:**

Diode **Type of Laser:**

IIIb **Laser Class - CDRH:**

## Physical & Mechanical Properties

71.0 L x 63.5 W x 19.8 H **Dimensions (mm):**

135.00 **Weight (g):**

<50 (8 Hours) **Pointing Stability ( $\mu$ rad):**

## Optical Properties

100:1 Linear **Polarization:**

632.80 **Wavelength (nm):**

1.1 (Horizontal)  
1.2 (Vertical) **Mode Quality,  $M^2$ :**

$\pm 0.5$  **Wavelength Tolerance (nm):**

0.8 x 1.6 **Beam Diameter (mm):**

Typical: 10 **Spectral Line Width (MHz):**

$\pm 0.002$  **Beam Stability (nm):**

1.3 x 0.8 **Beam Divergence (mrad):**

Red **Color:**

## Electrical

55 **Output Power (mW):**

1.00 **Power Stability (%):**

Max 5 **Power Consumption (W):**

$\pm 10$  **Output Power Tolerance (%):**

10 Hz - 100 MHz 0.2% RMS **Noise Level:**

Max 2 @ 3.3 V **Input Current (A):**

## Hardware & Interface Connectivity

10-pin Connectors (cable provided upon request) **Electrical Leads/ Pin Connections:**

USB **Computer Interface:**

Free Space **Output Type:**

## Environmental & Durability Factors

+15 to +40 **Operating Temperature ( $^{\circ}$ C):**

5 - 95% (non-condensing) **Operating Humidity:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Single Longitudinal Mode (SLM) Performance
- $\pm 0.002$ nm Wavelength Stability
- Very Low Power Consumption

632.8nm Frequency Stabilized Laser Diodes are ideal for typical HeNe laser applications including flow cytometry, interferometry, confocal microscopy, fluorescence excitation, and Raman spectroscopy. Whereas a comparable HeNe laser would be larger, more expensive, and consume more power, the 632.8nm Frequency Stabilized Laser Diodes feature more compact designs,  $\pm 0.002$ nm wavelength stability, and either greater than 60mW power (free-space model) or greater than 20mW power (fiber coupled model). Additionally, these lasers utilize Variable Bragg Gratings (VBG) to lock the 632.8nm wavelength to a 10MHz linewidth.