

LightPath 354220 | 633nm Alignment, 0.25 NA Fiber Collimator w/ FC/PC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#67-720**

3-4 DAYS

-

1

+

€187⁰⁰

ADD TO CART

Qty 1-10	€187,00
Qty 11+	€165,00
Volume Pricing	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General	
354220	Lightpath Lens Code:
Fiber Collimator	Type:
#87-118	Lens Included:
Physical & Mechanical Properties	
5.50	Clear Aperture CA (mm):
Protective bevel as needed	Bevel:
304L Stainless Steel Housing	Construction:
11.00	Housing Diameter (mm):
17.1	Housing Length (mm):
Optical Properties	
11.00 @ 633nm	Effective Focal Length EFL (mm):
0.25	Numerical Aperture NA:
D-ZK3	Substrate: ☐
BBAR (600-1050nm)	Coating:
R _{abs} <1.0% @ 600 - 1050nm	Coating Specification:
40-20	Surface Quality:
2.00	f/#:
600 - 1050	Wavelength Range (nm):
Infinite	Conjugate Distance:
633	Alignment Wavelength (nm):
< 0.040	Transmitted Wavefront Error (λ, RMS):
Hardware & Interface Connectivity	
FC/PC	Connector:
Threading & Mounting	
M11 x0.5	Mount:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

PRODUCT DETAILS

- Easy to Integrate
- Models for FC/PC, FC/APC, and SMA Connections Available
- Four Wavelength Ranges Covering 350-1600nm

LightPath® Fiber Optic Collimators are designed to collimate light exiting a fiber to a desired beam diameter or spot size or to focus light into a fiber when used in reverse. The lenses are diffraction limited, so they can achieve spot sizes down to a few microns. Lenses also feature an antireflection coating for low back reflection. LightPath® Fiber Optic Collimators are designed so that they can be used in pairs to couple the input and output light of optical devices. Optimum performance for long-term use is ensured by the factory set and tested lens alignment. Typical applications can include use with fiber coupled lasers and pigtailed receptacles, as well as communications and data transfer.

TECHNICAL INFORMATION

