

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock #39-620 3-4 DAYS



1



€137,00

ADD TO CART

Qty 1-5

€137,00

Qty 6+

€121,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) 85
Back Surface: Commercial Polish
Reflection at DWL (%) 99.8
Coating Specification: R_{abs} >99.8% @ 355nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (355nm)
Design Wavelength DWL (nm): 355
Dimensions (mm): 6.35 x 6.35 +0.00/-0.10
Thickness (mm): 3.18 ±0.20
Angle of Incidence (°): 0-45
Substrate: Fused Silica (Coming 7980)
Damage Threshold, Reference: 5 J/cm² @ 355nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View