


[See all 4 Products in Family](#)

## 635nm 70 x 375mm META® holoOPTIX® FLEX Notch Filter



70 x375mm META® holoOPTIX® FLEX Notch Filter

Stock #23-035 CLEARANCE **5 In Stock**

€250<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€250,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Notch Filter **Type:**

#### Physical & Mechanical Properties

70 x375 **Dimensions (mm):**

0.31 **Thickness (mm):**

#### Optical Properties

Optical Density OD (Average):

>4.0

Center Wavelength CWL (nm):

635.00

Transmission (%):

84% (400-600nm)  
85% (700-1500)

Spectral Bandwidth @ OD1:

16 (Typical)

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- >OD 4.0 (Typical)
- Broad Transmission Range
- Unique Large Flexible Design
- META® refers to the registered trademark of Meta Materials Inc.

META® holoOPTIX® Notch Filters are ideal for laser analysis applications requiring specific wavelength rejection and high transmission of all other wavelengths. Available in either a standard 25.4mm rigid mounted configuration (STRATA) or in a unique 375mm x 70mm flexible configuration (FLEX), these filters can be used in fluorescence or Raman spectrometers to eliminate unwanted noise from the pump laser source to obtain the optimum signal-to-noise ratio. The flexible design can be easily cut for system prototyping and integration. META® holoOPTIX® Notch Filters center wavelengths can be tuned by adjusting the angle of incidence while maintaining consistent notch center wavelengths for both p- and s- polarizations, even at high angles of incidence.

## Technical Information

