

TECHSPEC® 6mm Dia. x -6mm FL, VIS-NIR Coated, Double-Concave Lens



Stock **#45-927** [CONTACT US](#)
[Other Coating Options](#)

- 1 + **€41,00**

ADD TO CART

Qty 1-9
€41,00
Qty 10+
€37,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-6.00
Substrate: NSF11
f#: 1.00
Numerical Aperture NA: 0.50
Coating: VIS-NIR (400-1000nm)
Type: Double-Concave Lens
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): -6.41
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.50
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <3
Clear Aperture CA (mm): 5.4
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Edge Thickness ET (mm): 2.29
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -9.74
Surface Quality: 40-20
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant