

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 6mm Dia. X -9mm FL, MgF₂ Coated, Double-Concave Lens



Stock #48-935 3-4 DAYS

[Other Coating Options](#)



1



€33,50

ADD TO CART

Qty 1-9

€33,50

Qty 10+

€30,25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-9.00
Substrate: N-BK7
f#: 1.5
Numerical Aperture NA: 0.33
Coating: MgF ₂ (400-700nm)
Type: Double-Concave Lens
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): -9.32
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.00
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <3
Clear Aperture CA (mm): 5.4
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Edge Thickness ET (mm): 1.79
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -9.47
Surface Quality: 40-20
Damage Threshold, By Design: 10 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant