

TECHSPEC®

6mm, f/5.6 Cw Series Fixed Focal Length Lens



6mm Focal Length



Stock **#15-623** 20+ In Stock

-

1

+

€418^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€418,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Cw Series

Series:

C-Mbunt compatible with O-ring 25mm ID x2mm		Note:
Fixed Focal Length Lens		Type:
Physical & Mechanical Properties		
Fixed		Iris Option:
51.40		Length (mm):
46.00		Maximum Diameter (mm):
46		Outer Diameter (mm):
1.2		Maximum Rear Protrusion (mm):
Optical Properties		
Horizontal: 62.1° Vertical: 47.7° Diagonal: 75.0°		Field of View at Max Sensor Format:
62.1°		Horizontal Field of View, 1/1.8" Sensor:
55.8°		Horizontal Field of View, 1/2" Sensor:
50.7°		Horizontal Field of View, 1/2.5" Sensor:
42.7°		Horizontal Field of View, 1/3" Sensor:
9.00		Maximum Image Circle (mm):
0.0060		Numerical Aperture NA, Object Side:
10 (9)		Number of Elements (Groups):
6.00		Focal Length FL (mm):
75 - ∞		Working Distance (mm):
f/5.6		Aperture (f/#):
425 - 675nm BBAR		Coating Specification:
21.52		Entrance Pupil Position (mm):
-33.64		Object Space Principal Plane (mm):
22.43		Image Space Principal Plane (mm):
6.87		Maximum Distortion (%):
-25.51		Exit Pupil Position (mm):
VIS		Lens Wavelength Range:
Sensor		
1/1.8"		Maximum Sensor Format:
2.74		Pixel Size (μm):
Threading & Mounting		
M30.5 x0.50 (Female)		Filter Thread:
C-Mbunt		Mount:
Environmental & Durability Factors		
IPX7 and IPX9K		Environmental Rating:
-20 to +60		Storage Temperature (°C):
		Type of Ruggedization:

Regulatory Compliance

[View](#) Certificate of Conformance:

PRODUCT DETAILS


- Up to 2/3", C-Mount Lens
- Waterproof (Cw) Versions of C Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- Designed to Eliminate the Need for a Protective Lens Cover

TECHSPEC® Cw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® C Series Fixed Focal Length Lenses](#). Designed to meet IEC Ingress Protection Codes IPX7 and IPX9K, these lenses withstand exposure to water up to 1 meter depth for 30 minutes and operate in close-range high pressure, high temperature water spray downs with the exception of all 3.5 and 4.5mm options which are IPX7. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface. To prevent moisture from entering the housing, the lenses are sealed with multiple O-rings. TECHSPEC® Cw Series Fixed Focal Length Lenses are designed for up to 7.5 MegaPixel, 2/3" sensors and are ideal for applications including food, pharma, automotive, and security. These lenses won the Bronze-Level 2021 Vision Systems Design Innovators Award.


Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a [VIS-NIR Broadband Anti-Reflection \(BBAR\) Coating](#).
- Ci Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- Cr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.
- Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- Cw Series: Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 and IPX9K.


TECHNICAL INFORMATION




#15-623, 6mm, f/5.6 Cw Series Fixed Focal Length Lens, Distortion Plot




#15-623, 6mm, f/5.6 Cw Series Fixed Focal Length Lens, Relative Illumination Plot




#15-623, 6mm, f/5.6 Cw Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#15-623, 6mm, f/5.6 Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 200mm Working Distance, f5.6



#15-623, 6mm, f/5.6 Cw Series Fixed Focal Length Lens, Depth of Field Plot, 200mm Working Distance, f5.6



#15-623, 6mm, f/5.6 Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f5.6



#15-623, 6mm, f/5.6 Cw Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f5.6