

**TECHSPEC® 6mm, f/4 Sealed UCw Series Fixed Focal Length Lens**



UCw Series Fixed Focal Length Lenses

Stock #70-590 **2 In Stock**

⊖ 1 ⊕ €282<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€282,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Ucw Series **Product Family:**

Fixed Focal Length Lens **Type:**

High Performance Lens with Compact Form Factor **Imaging Lens Type:**

**Physical & Mechanical Properties**

**Iris Option:**

Fixed	
40.10	Length (mm):
38	Maximum Diameter (mm):
38	Outer Diameter (mm):
3.82	Maximum Rear Protrusion (mm):
40.9	Maximum Length (mm):

## Optical Properties

60.0°	Horizontal Field of View @ Max Sensor Format:
60.0°	Horizontal Field of View, 1/2" Sensor:
54.6°	Horizontal Field of View, 1/2.5" Sensor:
45.4°	Horizontal Field of View, 1/3" Sensor:
34.2°	Horizontal Field of View, 1/4" Sensor:
8.00	Maximum Image Circle (mm):
0.01	Numerical Aperture NA, Object Side:
9 (8)	Number of Elements (Groups):
6.00	Focal Length FL (mm):
50 - ∞	Working Distance (mm):
f/4.0	Aperture (f/#):
M4 MgF <sub>2</sub>	Coating:
M4 MgF <sub>2</sub>	Coating Specification:
12.61	Entrance Pupil Position (mm):
17.55	Object Space Principal Plane (mm):
4.85	Image Space Principal Plane (mm):
-11.19	Maximum Distortion (%):
-23.26	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:

## Sensor

1/2.5"	Optimized Sensor Format:
1/2"	Maximum Sensor Format:
1.85	Pixel Size (µm):

## Threading & Mounting

M34 x 0.5 (Female)	Filter Thread:
M34 x 0.5 (Female)	Front Thread:
C-Mount	Mount:

## Environmental & Durability Factors

IPX7	Environmental Rating:
-20 to +60	Storage Temperature (°C):
<a href="#">For questions regarding operating temperature please contact our support team</a>	

Waterproof (IPX7)

Type of Ruggedization:

## Regulatory Compliance

[View](#)

Certificate of Conformance:

## Product Details

- Up to 1/2", C-Mount Lens
- Ultra-Compact (UC), High Resolution Lens for Small Sensors
- Waterproof Versions of UC Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7

TECHSPEC® UCw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® UC Series Fixed Focal Length Lenses](#), and are designed to meet IEC Ingress Protection Codes IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes. Additionally, their compact size provides high performance at an affordable cost without sacrificing quality or feel. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface and are sealed with multiple O-rings to prevent moisture from entering the housing. TECHSPEC® UCw Series Fixed Focal Length Lenses are ideal for applications in space constrained, harsh environments such as food inspection, security, medical, and factory automation.

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

**UC Series:** Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

**UCi Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.

**UCr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

**UCw Series:** Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.