

TECHSPEC® 7.16mm Silver and VIS 0° Coated, Mounted Corner Cube Retroreflector



Mounted N-BK7 Corner Cube Retroreflectors



Stock **#12-211** 3-4 DAYS

⊖ 1 ⊕

€285,00

ADD TO CART

Qty 1-5
€285,00
Qty 6+
€228,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcsec):
±10

Coating:

MS 0° & Silver with protective overcoat
Diameter Tolerance (mm): +0.0/-0.1
Substrate: ☐ N-BK7
Inner Diameter (mm): 7.20
Outer Diameter (mm): 25.40
Surface Quality: 60-40
Mounting Threads: (1) ¼-20, (1) #8
Type: Retroreflector
Housing Tolerance (mm): Outer Diameter: +0/-0.5, Height: ±0.25
Image Orientation: Left-Handed
Coating Specification: Reflective Surfaces: R _{abs} > 97% FROM400 - 2500nm @ 0° AOI R _{avg} > 98% FROM400 - 2500nm @ 0° AOI Entrance: R _{avg} ≤0.4% @ 425 - 675nm
Ray Deviation (°): 180
Wavelength Range (nm): 425 - 675
Surface Flatness (P-V): λ/8

Regulatory Compliance

RoHS 2015: Not Compliant
Certificate of Conformance: View