

TECHSPEC® 6mm Diameter x 12mm FL, 355nm Coated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCX Lenses

Stock **#87-932** 3-4 DAYS

[Other Coating Options](#)



1



€166,00

ADD TO CART

Qty 1-5

€166,00

Qty 6+

€133,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00 +0.00/-0.05

Effective Focal Length EFL (mm):
12.00 @ 587.6nm

Back Focal Length BFL (mm):

10.63
Coating: Laser V-Coat (355nm)
Coating Specification: R _{abs} <0.25% @ 355nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 20-10
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ/10
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.00 ±0.05
Edge Thickness ET (mm): 1.11
Radius R₁ (mm): 5.50
Clear Aperture CA (mm): 5.4
f/#: 2.00
Numerical Aperture NA: 0.25
Design Wavelength DWL (nm): 355
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 4 J/cm ² @ 10ns

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View