

[See all 14 Products in Family](#)

TECHSPEC[®]

75mm C VIS-NIR Series Fixed Focal Length Lens



Stock #74-054

NEW

CONTACT US

-

1

+

€480^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€480,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Fixed Focal Length Lens

Imaging Lens Type:

Compact Lens Coated for Visible to Near Infrared

Physical & Mechanical Properties

Iris Option:

Variable

Length (mm):

98.76

48.0	Maximum Diameter (mm):
48.0	Outer Diameter (mm):
7.24	Maximum Rear Protrusion (mm):
Optical Properties	
5.76°	Horizontal Field of View @ Max Sensor Format:
	Field of View at Max Sensor Format: Horizontal: 5.76° Vertical: 4.32° Diagonal: 7.19°
5.76°	Horizontal Field of View, 2/3" Sensor:
4.71°	Horizontal Field of View, 1/1.8" Sensor:
4.19°	Horizontal Field of View, 1/2" Sensor:
3.77°	Horizontal Field of View, 1/2.5" Sensor:
3.14°	Horizontal Field of View, 1/3" Sensor:
11.00	Maximum Image Circle (mm):
0.05111	Numerical Aperture NA, Object Side:
7 (6)	Number of Elements (Groups):
75.00	Focal Length FL (mm):
500 - ∞	Working Distance (mm):
f/2.0 - f/16.0	Aperture (f/#):
425 - 1000nm BBAR	Coating:
425 - 1000nm BBAR	Coating Specification:
63.265	Entrance Pupil Position (mm):
-15.01	Object Space Principal Plane (mm):
-64.79	Image Space Principal Plane (mm):
0.068	Maximum Distortion (%):
-31.983	Exit Pupil Position (mm):
VIS-NIR	Lens Wavelength Range:
VIS-NIR	Wavelength:

Sensor

2/3"	Maximum Sensor Format:
------	------------------------

Threading & Mounting

M43 x 0.75 (Female)	Filter Thread:
C-Mount	Mount:

Environmental & Durability Factors

-20 to +60	Storage Temperature (°C):
For questions regarding operating temperature please contact our support team	

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Compact (C) Broadband Lens for 425-1000nm Wavelength Range
- 3.5mm to 50mm Focal Length

TECHSPEC® C Series Fixed Focal Length VIS-NIR Lenses are designed for use in machine vision applications that require NIR or VIS-NIR performance, with the working distance and resolution requirements of factory automation and inspection in mind. Featuring large maximum apertures and a Broadband Anti-Reflection (BBAR) coating designed out to 1000nm, these high performance lenses can be used in even the most restrictive lighting conditions. TECHSPEC® C Series Fixed Focal Length VIS-NIR Lenses are manufactured to a high tolerance, resulting in greater levels of imaging performance and low lens-to-lens variation, assuring simple installing into multiple systems. By combining high optical performance, industrial features, and small package size, the C Series Fixed Focal Length VIS-NIR Lenses represent a new standard in factory automation optics.

Also available with a [VIS Broadband Anti-Reflection \(BBAR\)](#) or [SWIR](#) Coatings

Note: For IR imaging alone, [UV-VIS Cut Filters](#) are available and thread directly onto the front filter threads of the 4.5mm, 16mm, 25mm, 35mm and 50mm FL lenses.

Technical Information

