

[See all 19 Products in Family](#)

## 70mm Dia Ring Light White

See More by [CCS](#)



CCS High-Angle LED Ring Lights

Stock **#21-781** **1 In Stock**

⊖ 1 ⊕ €1.220<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €1.220,00 each                |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

LDR2-70SW2 **Model Number:**

LED Illuminator **Type of Illumination:**

CCS **Manufacturer:**

High-Angle Ring Light **Geometry:**

Constant **Illumination Mode:**

## Physical & Mechanical Properties

OD: 70, ID: 35, Height: 22 **Dimensions (mm):**

120 **Weight (g):**

## Optical Properties

White **Color:**

## Electrical

7.6 **Power Consumption (W):**

## Hardware & Interface Connectivity

24 **Input Voltage (V):**

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#73-491](#)  
Europe: [#73-491](#)  
Japan: [#89-513](#)  
Korea: [#33-773](#)  
China: [#73-491](#)

## Environmental & Durability Factors

5500 **Color Temperature (K):**

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[Contains SVHC\(s\)](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

## Product Details

- High-Angle, Direct Lighting for Uniform Intensity
- Designed for Constant Output Power for Prolonged Use
- Ideal for Brightfield Illumination

CCS High-Angle LED Ring Lights provide illumination at a high angle of incidence for brightfield imaging applications. High density LED mounting and a flexible circuit board ensures uniform illumination intensity across all sizes of ring lights. These high-angle LED ring lights are designed to maintain constant output power over prolonged periods. CCS High-Angle LED Ring Lights alleviate the influence of slight differences in position or inclination of a sample for stable imaging and are ideal for industrial and manufacturing applications.

[3D-Printable Mount Files](#)



Ring Light Configuration

[Download Now](#)

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



[Application Note](#)

Illumination Mounts for Machine Vision Applications

[Read](#)




[Video](#)

Assembly of 3D Printed Mounts for Common Illumination Geometries

[Watch](#)

## Technical Information

### Imaging Example: Imaging Electrodes of Electronic Parts



|                       |                     |
|-----------------------|---------------------|
| Description           | Visual inspection   |
| Workpiece             | Electronic parts    |
| Conventional lighting | LED Bar Light       |
| New lighting          | LDR2-32RD2          |
| Result                | Improved uniformity |

Workpiece image




Electronic parts

LED Bar Light




It's difficult to make an image of the electrode part using a Bar Light.

LDR2-32RD2





A Ring Light can illuminate the electrode part evenly and make an image.


➤ Imaging Example: Imaging Text on Intake Valves



|                       |                                  |
|-----------------------|----------------------------------|
| Description           | Character recognition            |
| Workpiece             | Intake valves (automobile parts) |
| Conventional lighting | LED Ring Light                   |
| New lighting          | LDR2-50RD2                       |
| Result                | Emphasized characters            |

**Workpiece image**  
  
Intake valves

**LED Ring Light**  
  
It's difficult to clearly recognize the text due to the inner indentation.

**LDR2-50RD2**  
  
Allows for image that makes the character edges stand out.

;