


TECHSPEC® 75 x 100mm Protected Gold, 4-6λ Mirror



Stock **#48-458** ☐ In Stock

⊖ 1 ⊕ **€111,00**

ADD TO CART

Qty 1-5
€111,00

Qty 6+
€99,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):

75.0 x 100.0
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 71.25 x 95.00
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00
Type: Flat Mirror
Wavelength Range (nm): 700 - 10000
Length (mm): 100.00
Width (mm): 75.00
Damage Threshold, Reference: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant