

TECHSPEC® 75mm Square, MgF₂ Coated, B270 Window

See More by [SCHOTT Optical Components](#)



Stock **#48-420** ☐ In Stock

-

1

+

€113,00

ADD TO CART

Qty 1-5

€113,00

Qty 6+

€90,50

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
58.3

Bevel:
Protective as needed

Clear Aperture CA (mm):
70.00 x 70.00

Dimensions (mm): 75.00 x 75.00
Thickness (mm): 3.00
Coating: MgF ₂ (632.8nm)
Coating Specification: R _{avg} ≤1.50% @ 632.8nm (N-BK7)
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 9.4 (+20 to +300°C)
Density (g/cm³): 2.56
Edges: Fine Ground
Index of Refraction n_d: 1.523
Knoop Hardness (kg/mm²): 500
Poisson's Ratio: 0.22
Substrate: B270
Surface Flatness (P-V): 1λ
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 400 - 700
Young's Modulus (GPa): 71.5
Length (mm): 75.00
Width (mm): 75.00
Damage Threshold, By Design: ☐ 10 J/cm² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant