


[See all 32 Products in Family](#)

750 - 900nm (Ti:Sapphire), 4-6mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal- π Shaper_TiS_Q-5

See More by [AdiOptica](#)



Stock #25-849 **1 In Stock**

- 1 + €2.830⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€2.830,00 each
Qty 5+	€2.520,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Focal- π Shaper_TiS_Q-5 **Model Number:**

Beam Shaper **Type:**

[#12-322](#)

Compatible Adapter:

Physical & Mechanical Properties

29.00 Length (mm):

50 Weight (g):

20 Clear Aperture CA (mm):

42.00 Diameter (mm):

2.5 - 4 Input Beam Diameter, $1/e^2$ (mm):

Optical Properties

>99 Transmission (%):

750, 900 Design Wavelength DWL (nm):

750 - 900 Wavelength Range (nm):

TEM₀₀ Input Beam Mode:

<1.5 Typical Input Beam Mode Quality, M²:

±20 Input Beam Divergence (mrad):

Electrical

0.2 Maximum Input Power, CW (kW):

Threading & Mounting

M30 x 0.75 Inner Thread:

M30 x 0.75 Outer Thread:

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 250:

Product Details

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica πShaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal-πShaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal-πShapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

Technical Information

