


76.2mm Dia., 8mm Thick, Uncoated, ISP Optics Calcium Fluoride (CaF₂) Window | CF-W-76-8

See More by [ISP Optics](#)



Stock **#24-534** CLEARANCE **3 In Stock**

-

1

+

€383^{,00}

ADD TO CART

Volume Pricing	
Qty 1+	€383,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Protective Window	Type:
CF-W-76-8	Model Number:

Physical & Mechanical Properties	
Protective as needed	Bevel:
85	Clear Aperture (%):
64.77	Clear Aperture CA (mm):
76.20 +0.00/-0.13	Diameter (mm):
8.00 ±0.13	Thickness (mm):
Fine Ground	Edges:
158.30	Knoop Hardness (kg/mm²):
<3	Parallelism (arcmin):
0.26	Poisson's Ratio:
75.8	Young's Modulus (GPa):

Optical Properties	
94.99	Abbe Number (v _d):
Random	Axis Orientation:
Uncoated	Coating:
1.434	Index of Refraction (n _d):
Calcium Fluoride (CaF ₂)	Substrate:
2λ	Surface Flatness (P-V):
40-20	Surface Quality:
300 - 8000	Wavelength Range (nm):

Material Properties	
18.85	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
3.18	Density (g/cm³):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Greater than 90% Transmission from 350nm-7µm
- Low Index of Refraction
- Low Solubility and Chemically Inert

ISP Optics Calcium Fluoride (CaF₂) Windows provide environmental protection for electronic systems and sensors across the IR spectrum. Calcium Fluoride features greater than 90% transmission from 350nm to 7µm and a low refractive index, allowing it to be used without an anti-reflection (AR) coating. These windows are fabricated with IR Grade Calcium Fluoride, featuring low absorption and a high damage threshold in the infrared spectrum. ISP Optics Calcium Fluoride (CaF₂) Windows offer low solubility and superior hardness compared to other fluoride-based substrates, making them ideal for applications featuring harsh environments including infrared spectroscopy systems and thermal imaging.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools
