

[See all 10 Products in Family](#)

## 76.2mm Dia., Aluminum Coated, Aluminum Substrate Mirror



Stock #47-119 **2 In Stock**

- 1 + €615<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€615,00 each
Qty 6-25	€550,00 each
Qty 26-49	€520,00 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Flat Mirror **Type:**

### Physical & Mechanical Properties

**Diameter (mm):**

76.20 +0.00/-0.38

12.70 **Thickness (mm):**

90 **Clear Aperture (%):**

<175 **Surface Roughness ( $\square$ ):**

### Optical Properties

0.4 - 12 **Wavelength Range ( $\mu\text{m}$ ):**

Metal **Coating Type:**

Protected Aluminum (400-12000nm) **Coating:**

400 - 12000 **Wavelength Range (nm):**

Aluminum 6061-T6 **Substrate:**

**Coating Specification:**  
 $R_{\text{avg}} > 85\%$  @ 400 - 700nm  
 $R_{\text{avg}} > 70\%$  @ 700 - 2000nm  
 $R_{\text{avg}} > 97\%$  @ 2 - 12 $\mu\text{m}$

80-50 **Surface Quality:**

$\lambda/2$  **Surface Flatness (RMS):**

### Threading & Mounting

8-32 TPI Tapped Holes **Mounting Threads:**

### Regulatory Compliance

**RoHS 2015:**  
Compliant

**Certificate of Conformance:**  
[View](#)



**Reach 247:**  
Compliant

## Product Details

- Aluminum Substrate Mirrors
- Ideal for LWMR Laser Applications
- Aluminum and Gold Coating Options

Metal Substrate Mirrors are available with either a protected aluminum or gold coating and are ideal for LWMR (greater than 2000nm) laser applications. Due to the 17.5nm roughness of the diamond turned surface, these mirrors may not be suitable for UV and visible applications that require low scatter. The backs of the mirrors are machined flat and are tapped with 3 holes for easy, accurate mounting. Metal Substrate Mirrors are aluminum substrate, diamond turned metal mirrors. These mirrors are available in five diameters: 25.4, 38.1, 50.8, 76.2, and 101.6mm.

## Technical Information



## Compatible Mounts

---