

TECHSPEC® 75mm Dia., 0.33 Numerical Aperture NIR Coated, Aspheric Lens



Stock **#22-714** 3-4 DAYS

[Other Coating Options](#)



1



€800,00

ADD TO CART

Qty 1-5

€800,00

Qty 6+

€640,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
75.00 +0.0/-0.1

Effective Focal Length EFL (mm):
112.50 @587.6nm

Numerical Aperture NA:

0.33
Back Focal Length BFL (mm): 101.42
Substrate: N-BK7
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (600-1050nm)
Coating Specification: R _{avg} ≤1.5% @ 600 - 1050nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 67.5
Edge Thickness ET (mm): 4.13
Center Thickness CT (mm): 16.80 ±0.1
f#: 1.50
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 2200
Conjugate Distance: Infinite
Power (diopters): 8.89

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant