

[See all 17 Products in Family](#)

## 80 lp/mm, 1" x 3", Float Glass, Ronchi Ruling



Stock **#38-261** CLEARANCE **2 In Stock**

-

1

+

€240<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | €240,00 each                  |
| Qty 5+         | €228,80 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

| Product Downloads                |                    |
|----------------------------------|--------------------|
|                                  |                    |
| Physical & Mechanical Properties |                    |
| 3.00                             | Length (inches):   |
| 12.7 x 25.4                      | Pattern Size (mm): |
| 1.10                             | Thickness (mm):    |
| 1.00                             | Width (inches):    |

| Optical Properties      |                               |
|-------------------------|-------------------------------|
| Vacuum Deposited Chrome | Coating:                      |
| 80.00                   | Frequency (lp/mm):            |
| Float Glass             | Substrate:                    |
| 3.00                    | Optical Density OD (Average): |

| Regulatory Compliance     |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | Reach 240:                  |

## Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
  - Ideal for Reticle and Field Calibration Requirements
  - Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).
- Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.