

TECHSPEC® 75mm Dia. x 100mm FL, VIS 0° Coated, Achromatic Lens



Stock **#33-921** 3-4 DAYS

[Other Coating Options](#)



1



€347,50

ADD TO CART

Qty 1-5

€347,50

Qty 6+

€278,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
75.00 +0.0/-0.025

Effective Focal Length EFL (mm):

100.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 78.32
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 73.5
Centering (arcmin): <1
Center Thickness CT (mm): 38.70 ±0.20
Center Thickness CT 1 (mm): 26.00 ±0.10
Center Thickness CT 2 (mm): 12.7 ±0.10
Radius R ₁ (mm): 66.67
Radius R ₂ (mm): -66.67
Radius R ₃ (mm): -343.59
Edge Thickness ET (mm): 24.66
Substrate:  N-BAF10 / N-SF57
Surface Quality: 40-20
f/#: 1.33
Numerical Aperture NA: 0.38
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View