

800µm Low-OH Silica Core, 0.22 NA, High Power SMA Patch Cable, 2m



High Power Multimode Fiber Optic Patchcords

Stock #72-229 **1 In Stock**

- 1 + €286⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	€286,00 each
Qty 5-24	€257,40 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

HP SMA Patchcord **Type:**

Physical & Mechanical Properties

880 ±15 **Cladding Diameter (µm):**

44/148 (Short Term/Long Term) **Minimum Bend Radius (mm):**

2.00	Length (m):
800 ±20	Core Diameter (µm):
Stainless Steel	Jacket Material:
6.35	Jacket Diameter (mm):
1100 ±30	Buffer Diameter:
Optical Properties	
0.22 0.02	Numerical Aperture NA:
380 - 2200	Wavelength Range (nm):
Hardware & Interface Connectivity	
SMA	Connector:
Environmental & Durability Factors	
-40 to +90	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Low-OH Silica Core, 0.22 Numerical Aperture (NA)
- SMA Connector and Standardized 2m Length
- 380 – 2200 Wavelength Range

High Power Multimode Fiber Optic Patchcords are designed to enable high power light transmission by replacing energy-absorbing materials near the fiber end face such as epoxies, connector materials, and coatings with an air-gap-ferrule. These Patchcords are 2 meters in length and feature a 0.22 numerical aperture (NA), SMA connectors, and are available with core diameters of 200, 400, 600, and 800µm. These cables are also ideal for free-space-to-fiber applications where an input beam is fully contained in the fiber core and is within the fiber's NA. High Power Multimode Fiber Optic Patchcords are designed to work with laser light sources within the broadband 380 – 2200 wavelength range. These cables are ideal for beam delivery, microscopy, fiber optic sensing, and telecommunications applications.

Note: These cables should not be combined with low-power fiber patch cables and should not be used in mating sleeves or with fixed attenuators.