

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 75mm Dia. X 200mm FL, VIS 0⁺, Inked, Achromatic Lens



Stock #88-593-INK ☒ In Stock
[Other Coating Options](#)



1



€357,50

ADD TO CART

Qty 1-5
€357,50

Qty 6+
€286,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
75.00 ±0.025

Effective Focal Length EFL (mm):

200.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 187.69
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 73.5
Centering (arcmin): <1
Center Thickness CT (mm): 23.94 ±0.20
Center Thickness CT 1 (mm): 17.94 ±0.10
Center Thickness CT 2 (mm): 6.00 ±0.10
Radius R ₁ (mm): 118.81
Radius R ₂ (mm): -96.37
Radius R ₃ (mm): -288.97
Edge Thickness ET (mm): 15.42
Substrate:  N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 2.67
Numerical Aperture NA: 0.19
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View