

8mm Dia. x 5.6mm FL, Aspheric Condenser Lens



Stock **#19-510** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

€36^{.05}

ADD TO CART

Volume Pricing	
Qty 1-10	€36,05 each
Qty 11-49	€32,96 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:
Condenser Lens

Physical & Mechanical Properties

8.00 +0.0/-0.2	Diameter (mm):
≤30	Centering (arcmin):
7.2	Clear Aperture CA (mm):
1.33	Edge Thickness ET (mm):
4.00 ±0.30	Center Thickness CT (mm):
Protective as needed	Bevel:
8	Diameter of Asphere (mm):
Convex	Shape of Back Surface:
Optical Properties	
5.60	Effective Focal Length EFL (mm):
0.71	Numerical Aperture NA:
3.3	Back Focal Length BFL (mm):
H-ZK2	Substrate:
±5	Focal Length Tolerance (%):
Uncoated	Coating:
80-50 (typical)	Surface Quality:
0.7	f/#:
16.52	Radius R ₂ (mm):
350 - 2000	Wavelength Range (nm):
Infinite	Conjugate Distance:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

TECHNICAL INFORMATION



