

**TECHSPEC® 800 - 1200nm, 25.2 x 35.6mm, Dichroic Shortpass Filter Kit (9 Filters)**



Stock #15-111 [CONTACT US](#)

- 1 + **€1.325,00**

ADD TO CART

|           |
|-----------|
| Qty 1+    |
| €1.325,00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Dimensions (mm):**  
25.2 x 35.6

**Filters Included :**  
Cut-off Wavelengths: [800nm](#), [850nm](#), [900nm](#), [950nm](#),  
[1000nm](#), [1050nm](#), [1100nm](#), [1150nm](#), [1200nm](#)

**Length (mm):**  
35.60

**Type:**  
Shortpass Filter

|                                                                                                                                                                                  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Width (mm):</b><br>25.20                                                                                                                                                      |
| <b>Number of Filters:</b><br>9                                                                                                                                                   |
| <b>Environmental Durability:</b><br>Humidity per ML-STD-810H, Section 507.6<br>Temperature per ML-STD-810H, Section 501.7 and 502.7                                              |
| <b>Physical Durability:</b><br>Adhesion per ML-PRF-13830B, Section C.4.5.12<br>Moderate abrasion per ML-PRF-13830B, Section C.4.5.11<br>Cleaning per ML-C-48497A Section 4.5.4.2 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---