

[See all 13 Products in Family](#)

## 88mm Dia x 134mm FL Cold Mirror Coated, Ellipsoidal Reflector



Precision Ellipsoidal Reflectors

Stock **#68-800** **1 In Stock**

⊖ 1 ⊕ €400<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1-10   | €400,00 each                  |
| Qty 11-25  | €350,00 each                  |
| Qty 26-49  | €330,00 each                  |
| Need More? | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Specialty Mirror **Type:**

### Physical & Mechanical Properties

20.0 **Center Hole Diameter (mm):**

**Height (mm):**

46.0

81 Inner Diameter (mm):

88.00 +0.0/-0.5 Outer Diameter (mm):

### Optical Properties

Metal Coating Type:

Cold Mirror, 0° Coating:

BOROFLOAT® Substrate: □

14 Distance to Focal Point f<sub>1</sub> (mm):

134 Distance to Focal Point f<sub>2</sub> (mm):

### Regulatory Compliance

View Certificate of Conformance:


## Product Details

- Precision Polished Substrate
- Protected Aluminum and Cold Mirror Coating Options
- Ideal for Solar and Condensing Applications
- [Precision Parabolic Reflectors](#) Also Available

Precision Ellipsoidal Reflectors are ideal for simplifying system design and integration. By having two focal points, ellipsoidal mirrors eliminate the need for multiple focusing components within an assembly. When a light source is placed at the first focal point, the source will refocus at the second focal point. Precision Ellipsoidal Reflectors are available with two mirror coating options. The protected aluminum coating features broadband high reflection through the visible and IR spectra. The cold mirror coating reflects visible light while transmitting NIR, making it ideal for cold condensing applications.

Precision Ellipsoidal Reflectors are precision polished, yielding exact aspheric profiles. These mirrors offer improved thermal stability and superior focusing efficiency versus commercially available press-molded reflectors. Typical applications include use as steppers for PCB, LCD, or PDP production, solar simulators, fiber optic illuminators, and projectors.

## Technical Information



| Diameter | x      | y     | Hole Size d | Height H | A     | B     | Stock No.               |
|----------|--------|-------|-------------|----------|-------|-------|-------------------------|
| 64mm     | 11mm   | 78mm  | 18mm        | 44mm     | 31mm  | 36mm  | <a href="#">#90-968</a> |
|          |        |       |             |          |       |       | <a href="#">#90-973</a> |
| 86mm     | 14mm   | 134mm | 20mm        | 48mm     | 32mm  | 88mm  | <a href="#">#68-797</a> |
|          |        |       |             |          |       |       | <a href="#">#68-800</a> |
| 105mm    | 22mm   | 145mm | 27mm        | 42mm     | 20mm  | 103mm | <a href="#">#90-969</a> |
|          |        |       |             |          |       |       | <a href="#">#90-974</a> |
| 115mm    | 17mm   | 272mm | 26mm        | 54mm     | 36mm  | 219mm | <a href="#">#68-798</a> |
|          |        |       |             |          |       |       | <a href="#">#68-801</a> |
| 128mm    | 18mm   | 288mm | 31mm        | 67mm     | 50mm  | 220mm | <a href="#">#90-970</a> |
| 150mm    | 22.5mm | 360mm | 40mm        | 70mm     | 48mm  | 290mm | <a href="#">#90-971</a> |
|          |        |       |             |          |       |       | <a href="#">#68-802</a> |
| 220mm    | 40mm   | 440mm | 60mm        | 90mm     | 53mm  | 347mm | <a href="#">#68-799</a> |
|          |        |       |             |          |       |       | <a href="#">#68-803</a> |
| 300mm    | 45mm   | 800mm | 80mm        | 147mm    | 108mm | 647mm | <a href="#">#90-972</a> |

