

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 980nm CWL, 25mm Dia, 3.7 nm Bandwidth, OD 6 Laser Line Bandpass Filter



Stock #68-983 CONTACT US

[Additional Bandwidths](#)



1



€665,00

ADD TO CART

Qty 1-9

€665,00

Qty 10+

€585,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Angle of Incidence (°):
0 ±2

Bandwidth (nm):

3.7
OD 5 Blocking Wavelength Range (nm) : 724.4 - 970.2 & 989.8 - 1332.6
OD 6 Blocking Wavelength Range (nm): 901.6 - 965.3 & 994.7 - 1078
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 21.00
Center Wavelength CWL (nm): 980.00
Design Wavelength DWL (nm): 980
Full Width-Half Max FWHM (nm): 6.90
Substrate: ☐ Fused Silica (Corning 7980)
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): +0.0/-0.1
Transmission (%): ≥90
Type: Bandpass Filter
Durability: Environmental: MIL-STD-810F, sect. 507.4 Durability: MIL-C-48497A, sect. 3.4.1
Transmitted Wavefront, RMS: <i>N4</i> @ 633nm
Mount Thickness (mm): 3.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View