

TECHSPEC®

9.0mm Diameter x 13.5mm FL, 1064nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock **#66-267** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

€46,50

ADD TO CART

Qty 1-9
€46,50

Qty 10+
€41,75

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm): 13.50 @ 587.6nm
Back Focal Length BFL (mm): 11.94
Coating: Laser V-Coat (1064nm)
Coating Specification: R _{abs} <0.25% @ 1064nm
Substrate: ☐ N-SF5
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.60 ±0.05
Edge Thickness ET (mm): 1.41
Radius R₁ (mm): 9.09
Clear Aperture CA (mm): 8.1
f/#: 1.5
Numerical Aperture NA: 0.33
Design Wavelength DWL (nm): 1064
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 5 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant