

[See all 5 Products in Family](#)

## 9mm Dia. x 36mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-073 CLEARANCE **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €20<sup>50</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€20,50 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Plano-Convex Lens **Type:**

### Physical & Mechanical Properties

9.00 +0.00/-0.10 **Diameter (mm):**

6.00 **Centering (arcmin):**

**Edge Thickness ET (mm):**

1.15

Clear Aperture CA (mm):

≥7.65

## Optical Properties

Effective Focal Length EFL (mm):

36.00

Back Focal Length BFL (mm):

34.89

Coating:

MgF<sub>2</sub> (400-700nm)

Coating Specification:

R<sub>avg</sub> ≤ 1.75% @ 400 - 700nm

Substrate: □

N-BK7

Focal Length Tolerance (%):

±1

Radius R<sub>1</sub> (mm):

18.61

f#:

4.00

Numerical Aperture NA:

0.13

## Regulatory Compliance

Certificate of Conformance:



[View](#)

## Product Details

- Feature Standard Designs and Specifications
- Also Available [Uncoated](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. MgF<sub>2</sub> anti-reflection coating offers improved transmission in the visible spectrum. Commercial Grade MgF<sub>2</sub> Coated Plano-Convex (PCX) Lenses offer commercial quality, at an affordable price.

## Technical Information



## Coating Curves